

Planetary Centrifugal Mixer

THINKY MIXER ARM-310 < €



Reproducibility, Homogeneity, Effectivity by 400G

- Mixing a wide range of materials from low to high viscosity
- Shortening the time for mixing and improving overall working process
- Compatible with 3 ml 300 ml syringe/container
- 70 standard container, 30 standard adapters
- Custom-made adapters available fits your container









Specifications

Product Name	Planetary centrifugal mixer "THINKY MIXER"
Model	ARM-310 CE
System	Planetary, propeller-less mixing
Operation Time Setting	Timer setting range: 0 s to 30 min in 1 s increments
Programming Function	STD mode: 5 memories with 1 step STEP mode: 5 memories with 5 steps
Payalution enood (rnm)	STD mode (2000 rpm fixed)

STEP mode (0, 200-2000 rpm)

Maximum Capacity		310g
Standard	d Container	300 ml resin container
Power Supply	Voltage	Single-phase AC230 V ± 10%, 50 Hz
	Power Consumption	Approx. 50 VA (standby) Max 900 VA (operation)
Operating Environment		10 to 35 °C, 35 to 85 % RH (without condensation)
Unit Dimensions		H390 × W300 × D340 (mm)
Unit Weight		Approx. 21 kg

THINKY CORPORATION

Head quarters: 2-16-2 Sotokanda, Chiyoda-ku, Tokyo 101-0021 Phone: +81-3-5207-2713 Fax: +81-3-5289-3281

THINKY USA Inc.: 23151 Verdugo Drive, Suite 112 Laguna Hills, CA92653, USA THINKY CHINA: East building, HaiAn Kafunuo Mansion, Shennan road, Qianhai road, Nanshan district, Shenzhen

Max. 800 rpm

http://www.thinkymixer.net/

Email: info@thinkymixer.net

Rotation Speed (rpm)



Qi srl

t +39 06 9105461

www.qitech.it | SalesQi@qitech.it